

Ez SHOT HD

Easy to Use

Auto Focus HD intraoral camera



Wired type



-IC-WHT60
-IC-DCAM70
-IC-WHC50
-IC-EZAU81

-IC-WHW61
-IC-DCAU71
-IC-EZAM80

-CL-DLT30
-CL-DC20

-CL-DL10
-CL-AT24

-AL-DF10

Easy to Use

Auto Focus HD intraoral camera

1 Features of Ez SHOT HD

Wireless type only



High speed digital wireless

High speed digital wireless provide more clear live image without interruption.



Wireless receiver

Compact wireless receiver without any power supply.



Auto focus

Can get clear image with auto focus function in oral cavity.



HD image

Can get high definition image without distortion.



Adjustable LED brightness

To avoid image quality loss by light reflection, can adjust LED brightness.



Black & White function

Can take and send analog X-ray film image to PC.



Plug & Play

No need additional driver to install the device.



Easy to capture

Easy to image capture by camera only without extra device like foot pedal.



Software compatibility

Can be use camera with most of dental imaging software.

* It would need twain driver for some of dental imaging software.



Wireless



Wired

2 Specification

Model name		IC-EZAM80(Wireless model)
Camera	Operation voltage	3.7V
	Size	Approx. 255 x 27 x 29 mm
	Weight	Approx. 89g
	Resolution	1.3 Mega pixel
	Sensor/Lens type	CMOS / Liquid lens
Charger	Operation voltage	5V
	Size	Approx. 110 x 105 x 68 mm
	Weight	Approx. 100g
Disposable cover	Size	Approx. 32 x 100 mm
	Quantity	Approx. 100 pcs by weight x 2ea
	Raw material	Polyethylene

Model name		IC-EZAU81(Wired model)
Camera	Operation voltage	5V
	Size	Approx. 202 x 27 x 29 mm
	Weight	Approx. 55g
	Resolution	1.3 Mega pixel
	Sensor/Lens type	CMOS / Liquid lens
USB cable	Length	Approx. 3M
Disposable cover	Size	Approx. 32 x 100 mm
	Quantity	Approx. 100 pcs by weight x 2ea
	Raw material	Polyethylene

3 Minimum System Requirement

PC system:	2.0 Ghz CPU, 1GB RAM
OS:	Windows XP service pack 3
USB port:	USB 2.0



Upper images are take by real product.

4 DrsViewer2

Image Viewer included.

